



UNiLUX


EYELIGHT


EYELIGHT black



EYELIGHT and color t° according to its light needs for different activities (work on screen, reading, relaxation ...) is controlled by the My unilux mobile application. In automatic mode, it regulates the light oculator's t° throughout the day; based on the user's pre-programmed circadian cycle; thus promoting its well-being and better health. The manual mode allows you to adjust, at your convenience; the intensity

EYELIGHT grey metal





Free upload application : My-unilux



- **Well-being:** innovative and connected lamp via your smartphone that synchronizes your circadian rhythm by reproducing sunlight and its impact on hormones (melatonin and serotonin).
- **Automatic mode:** The pre-programmed circadian cycle brings you the right quality of light at the right time of day.
- **Manual mode:** adjustment of intensity and color temperature according to your needs.
- **Convenient to use:** the intensity is fully adjustable, simply touch the touch button under the head to adjust the intensity of the light.
- **Trendy and functional design:** its slender and dynamic lines will seduce many users.
- **Low visual stress after prolonged use:** ideal for working, reading or studying, at home or in the office.
- **Available in two colors:** black or metal grey


Warranty: 2 years
 Maximum height: 62 cm / minimum height: 37 cm
 Materials: ABS plastic base / aluminum arm and head




Professional replaceable light source (LED only)

Characteristics


Measurement of Lux on the worktop in 35 cm top view:



Measurement of Lux on the worktop in 35 cm profile view:



Measurement in nanometers of the light spectrum




- 0 No-risk
- 1 Low-risk
- 2 Moderate-risk
- 3 High-risk

SAP. code	400093835	400095547
EAN code	3595560015672	3595560026005
Colors	Black	Grey metal
Luminous flow (Lm)	533	533
Lux (Lx)	1950	1950
Luminous Efficiency (Lm/W)	76	76
Color T° (K)	2700 K at 5200 K	2700 K at 5200 K
CRI	86	86
Source's lifetime (h)	50 000	50 000
Energy Consumption (kWh/1000h)	7	7
USB port	No	No
Induction charger	No	No
Net weight (kg)	1,92	1,92

OUR CSR COMMITMENTS

1. All our lighting are **100% repairable** thus limiting planned obsolescence.
2. Reduce our carbon footprint through our **ECO-DESIGN THINKING** approach.
3. Contribute to the preservation of the planet's natural resources by promoting the use of **recycled materials**.
4. Optimize our packaging to control our **transport costs**.
5. Highlight the **talent of our employees** by ensuring social equality.

Energy class




OUR EXPERTISE

1-Why use accent lighting?

We are regularly subjected to constant artificial lighting in the office that does not take into account our biological rhythm. Poor lighting quality can cause headaches, sleep disorders, loss of concentration. According to a recent study, only 34% of offices reach the lighting level of 500 lux recommended by Occupational Medicine.

2-Biodynamic light: source of well-being!

An adapted biodynamic light that accompanies you on a daily basis is essential to be effective in your work, your projects in order to prevent any harmful consequences produced by poor lighting. Your productivity will be greatly improved, you will be more dynamic and in a better mood. This is the reason why each individual must carefully follow his "circadian rhythm". The circadian rhythm is a biological rhythm that governs a set of physiological processes in humans. It is regulated by light for 24 hours.



OUR CERTIFICATIONS

Unilux is committed to an eco-responsible approach and ensures that its products respect this commitment. Indeed, we are very concerned about current environmental issues and we aspire to respond as best as possible to the concerns of our consumers on this subject. Sustainable development is at the heart of our strategy and we act for the environment. You will find below the different certifications that Unilux has and that prove its environmental commitment.



30 products available on pCon Planner

You will be able to obtain data on many UNILUX or OFML standard products and integrate them quickly and easily into 3D space layouts via pCon.



Download on our E-shop

Always available: photos in HD, data sheets, instruction manual, repairability instructions for all our products.



Do you have any questions?

Our after-sales service is always at your disposal

Tèl: +33 1 81 86 06 03

E-mail: contact.unilux@hamelinbrands.com

17 avenue du Parc TECHNOPOLIS

91380 Chilly Mazarin – France

Tèl: +33 1 81 86 06 00

www.my-unilyx.com

E-mail: contact.unilux@hamelinbrands.com

UNILUX